

MR3919-000-US | FDSC-GATOR-12F-T



Gator 12F Fiber Optic Splice Closure, Re-enterable, Gel Cable sealing, for up to 12 splices, Build America Buy America (BABA)

- Designed for splicing two loose tube “flat drop” style cables of 1 to 12 fibers in above grade, below grade, and direct buried applications
- Uses gel sealing technology to create a sealed closure system that will fit into confined areas such as small “flowerpot” style handholes
- Incorporates our unique cable hold down and strength member termination features and is capable of holding either fusion or mechanical splices
- Tone wires can also be terminated outside of the closure using the included hardware
- *CommScope intends to release this product at a future date. At such time, this product will comply with the requirements of the Build America, Buy America Act and/or applicable waivers. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability	Latin America North America
Product Type	Single-ended, flat fiber closure
Product Series	FDSC GATOR
Government Funding	Build America Buy America (BABA) coming soon*

General Specifications

Cable Entry Drop Port Style	Flat
Cable Entry Main Port Style	Flat
Cable Ports Quantity, total	2 round ports
Cable Sealing Type	Compressed gel
Closure Sealing Type	Hinged with latch
Closure Style	Single-ended
Color	Black
Mounting	Wall
Network Area Type	Drop
Splicing Capacity, Mass Fusion, maximum	12
Splicing Capacity, Single Fusion, maximum	12
Splicing Type, Supported	Mass fusion Single fusion

Dimensions

MR3919-000-US | FDSC-GATOR-12F-T

Height	30.48 mm 1.2 in
Width	147.32 mm 5.8 in
Length	190.5 mm 7.5 in

Environmental Specifications

Environmental Space	Below ground Buried
----------------------------	-----------------------

Packaging and Weights

Packaging quantity	10
Packaging Type	Box Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

