

# A-100606

## Base Product



## Meter Cabinet, empty

- Sealed to outside environment
- Double wall construction

## Product Classification

### Product Type

Power supply enclosure

## General Specifications

### Access

Front door

### Accessories

Cable plate | In-ground root | Plinth

### Batteries Supported

0

### Batteries Supported, with optional battery pedestal

0

### Cabinet Type

Meter cabinet

### Color

Green | Green (RAL 6009) | Light Gray (RAL 7035) | Others available at additional cost

### Door Security

7 mm triangle lock

### Internal Mounting Surface

12 mm plywood backboard

## Dimensions

### Height

1016 mm | 40 in

### Width

660.4 mm | 26 in

### Depth

254 mm | 10 in

### Depth, without door

254 mm | 10 in

## Electrical Specifications

### ac Feeds, Outgoing, quantity

0

### Generator Connection

No connection

## Material Specifications

### Finish

Powder coated

### Material Type

Galvanized steel

# A-100606

---

## Packaging and Weights

**Weight, net**

35.834 kg | 79 lb

## Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system