

# F1-PNMNM-HF

---

FSJ1-50A Jumper with interface types N Male and N Male, variable length



## Product Classification

|                       |                    |
|-----------------------|--------------------|
| <b>Product Type</b>   | SureFlex® standard |
| <b>Product Series</b> | FSJ1-50A           |

## General Specifications

|   |          |
|---|----------|
| <b>Body Style, Connector A</b>            | Straight |
| <b>Body Style, Connector B</b>            | Straight |
| <b>Interface, Connector A</b>             | N Male   |
| <b>Interface, Connector B</b>             | N Male   |
| <b>Specification Sheet Revision Level</b> | A        |

## Dimensions

|                     |            |
|---------------------|------------|
| <b>Length</b>       | 0 m   0 ft |
| <b>Nominal Size</b> | 1/4 in     |

## VSWR/Return Loss

| <b>Frequency Band</b> | <b>VSWR</b> | <b>Return Loss (dB)</b> |
|-----------------------|-------------|-------------------------|
| <b>10–18000 MHz</b>   | 1.671       | 12                      |

## Jumper Assembly Sample Label

# F1-PNMNM-HF

---



## Environmental Specifications

### Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

## Included Products

- F1PNM-HF – Type N Male for 1/4 in FSJ1-50A cable