



CHD 1U fixed fiber panel, accepts (12) CHD ULL modules, splice cassettes or MPO panels, providing up to 72 duplex LC ports or up to 72 MPO ports, black, High Speed Migration

Product Classification

Regional Availability	China
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	CHD

General Specifications

Application	Accepts 12 CHD Universal Modules, or CHD MPO/LC adapter packs
Color	Black
Rack Type	EIA 19 in
Rack Units	1
Shelf Movement	Fixed

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	212.2 mm 8.354 in

Material Specifications

Finish	Powder coated
Material Type	Steel

Environmental Specifications

Flammability Rating	UL 94 V-0
----------------------------	-----------

760248335 | CHD-ES-1U

Packaging and Weights

Packaging quantity 1

Weight, net 1.56 kg | 3.44 lb