

# CM-R78

---



## Round Chimney Mount, 7-8 ft OD

### Product Classification

**Product Type** Chimney mount

### General Specifications

**Mounting** Round Chimneys, 2.13-2.44 m (7-8 ft) OD

### Dimensions

**Height** 609.6 mm | 24 in

**Width** 1524 mm | 60 in

**Length** 1524 mm | 60 in

### Material Specifications

**Material Type** Hot dip galvanized steel

### Mechanical Specifications

**Wind Rating** For Specifications, please contact [steelproducts@commscope.com](mailto:steelproducts@commscope.com) or call 800-255-1479

**Wind Rating Test Method** TIA/EIA-222

### Packaging and Weights

**Included** Brackets | Hardware

**Packaging quantity** 1

**Weight, net** 136.1 kg | 300.049 lb

### Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system

# CM-R78

---



\* Footnotes

**Wind Rating**

BWS—Base Wind Speed; FBC—Florida Building Code