

ST-SVPEH30



Solar/Video Hinged Embedded Communication Pole, 30 ft

- Hinged design
- No climbing necessary for equipment installation
- Single person service
- Secure locking

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Monopole
Ordering Note	CommScope® non-standard product
Warranty	One year

General Specifications

Application	Solar Supervisory Control and Data Acquisition (SCADA)/Video surveillance
Equipment Load Rating	Omni antenna Solar panel Telecommunications unit
Foundation	Base
Monopole Capability Type	Light duty
Monopole Design	Round conical
Optional Accessories	Antenna mounts Cabinet mounts Helical base foundation Solar mounts Video mounts

Dimensions

Height	9.144 m 30 ft
Mounting Diameter, maximum	208.28 mm 8.2 in
Mounting Diameter, minimum	83.82 mm 3.3 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Mechanical Specifications

Wind Rating Test Method	TIA/EIA-222-G
--------------------------------	---------------

ST-SVPEH30

Packaging and Weights

Included	Ground tab Hand holes Lightning rod Monopole
Packaging quantity	1
Weight, net	203.5 kg 448.64 lb

* Footnotes

Warranty For more information, please consult our Product Warranty guidelines