

460201084



Fiber Optic Connector, SN/UPC for 1.6 mm cable

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio

CommScope®

Product Type

Fiber connector

General Specifications

Color, boot

Black

Color, housing

Navy blue

Interface

SN/UPC

Dimensions

Length

50.9 mm | 2.004 in

Compatible Cable Diameter

1.5 mm | 0.059 in | 1.6 mm | 0.063 in

Material Specifications

Ferrule Material

Zirconia

Mechanical Specifications

Cable Retention Strength, maximum

11.24 lb @ 0 °

Optical Specifications

Fiber Mode

Singlemode

Fiber Type

G.657.A2

Optical Components Standard

ANSI/TIA-568. 3-D | IEC 61753-1

Insertion Loss, maximum

0.25 dB

Return Loss, minimum

50 dB