



iPatch® M4200i 24 Port UTP Intelligent Universal Modular Panel without Modules

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	RJ45 patch panel
Product Brand	iPatch® imVision®

General Specifications

ANSI/TIA Category	6 6A
Cable Type	Unshielded
Color	Black
Intelligence Type	iPatch® enabled
Panel Style	Straight
Rack Units	1
Total Ports, quantity	24

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	25.4 mm 1 in

Material Specifications

Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate
----------------------	---

Environmental Specifications

Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing

760073866 | iP-M4200i-24

Flammability Rating UL 94 V-0

Safety Standard ACMA | CE | UL | cUL

Packaging and Weights

Included Cable management bar | Four #12-24 dog point mounting screws | Information outlet removal tool | Instruction sheet | Panel | Two #12 washers | Two #12-24 screws

Packaging quantity 1

Weight, net 0.68 kg | 1.5 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

ROHS

UK-ROHS

Classification

Designed, manufactured and/or distributed under this quality management system

Compliant/Exempted

Compliant/Exempted

