

760239069 | UDS-2U-WH-LA-B



UDS 2RU splice panel, 144 duplex LC/APC ports, Enhanced Method B

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	UDS

General Specifications

Application	Preloaded with 12 UDS modules
Color	White
Intelligence Type	Not iPatch® ready
Interface, front	LC/APC
Pigtail Assembly Type	12-fiber, ribbon
Pigtails Included, quantity	12
Rack Type	EIA 19 in
Rack Units	2
Shelf Movement	Sliding
Splice Trays Included, quantity	4
Total Ports, quantity	144

Dimensions

Height	88.9 mm 3.5 in
Width	444.5 mm 17.5 in
Depth	609.6 mm 24 in

Optical Specifications

Insertion Loss, maximum	0.4 dB
--------------------------------	--------

Environmental Specifications

Safety Standard cUL US 1863

Packaging and Weights

Packaging quantity 1

Weight, net 6.804 kg | 15 lb

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Above maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

