

760082503 | RK6-52A



Equipment Rack, 2-Post, 6 in (152 mm) Channel x 8 ft (2438 mm) H - 19 in (482.6 mm) Alu (52U) 12-24 Tapped Rails, Black

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	2 post rack

General Specifications

Color	Black
Rack Type	EIA 19 in
Rack Units	52
Rail Mounting Hole	#12-24

Dimensions

Height	2,438.4 mm 96 in
Channel Width	152.4 mm 6 in
Width	518.16 mm 20.4 in
Depth	457.2 mm 18 in
Dimensional Standards	EIA-310-E

Material Specifications

Finish	Powder-coated, textured
Material Type	Aluminum

Mechanical Specifications

Static Load Rating	453.6 kg 1,000.016 lb
---------------------------	-------------------------

Packaging and Weights

Included	Forty #12-24 x 1/2 in mounting screws Instruction sheet Twelve 3/8 in split lock washers Twelve 3/8-16 UNC x 1 in hex head bolts Twelve 3/8-16 hex nuts Two extruded base
-----------------	---

760082503 | RK6-52A

angles | Two extruded top angles | Two vertical rack rails

Packaging quantity	1
Packaging Type	Flat packed
Weight, net	16.33 kg 36.001 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

