



## ION® Active Intelligent Point of Interface Subrack with Guide Rails

### Product Classification

<b>Product Type</b>	Point of interface subrack
<b>Product Brand</b>	ION®

### General Specifications

<b>General Alarm</b>	Integrated into management system
<b>Interface Slots Available, quantity</b>	1
<b>Mounting</b>	Rack
<b>Note</b>	Detailed Product Specifications are available. Please contact your local CommScope representative.
<b>Rack Type</b>	EIA 19 in
<b>Slots Available, quantity</b>	8

### Dimensions

<b>Height</b>	177 mm   6.969 in
<b>Width</b>	483 mm   19.016 in
<b>Depth</b>	422 mm   16.614 in

### Electrical Specifications

<b>Electrical Safety Standard</b>	EN 60950
<b>Power Consumption</b>	276 W
<b>Voltage Range</b>	+10 to +14 Vdc

### Environmental Specifications

<b>Operating Temperature</b>	+5 °C to +55 °C (+41 °F to +131 °F)
------------------------------	-------------------------------------

<b>Storage Temperature</b>	-25 °C to +70 °C (-13 °F to +158 °F)
<b>Relative Humidity</b>	46%–94%
<b>Mean Time Between Failures (MTBF) at Temperature</b>	213,000 h @ 25 °C

## Packaging and Weights

<b>Height, packed</b>	530 mm   20.866 in
<b>Width, packed</b>	295 mm   11.614 in
<b>Depth, packed</b>	600 mm   23.622 in
<b>Included</b>	Guide rails
<b>Weight, gross</b>	8 kg   17.637 lb
<b>Weight, net</b>	7 kg   15.432 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system