ATC200-LITE-USB-EU



Portable Controller for EU & UK

- Carried from site to site for RET antenna setup and optimization
- Supports up to 32 RET actuators operating in a mix of AISG modes
- LED display indicates the presence of input power, output power, and data communication
- Equipped with USB and serial connectors
- Power supply efficiency is Energy Star® Level IV rated

Product Classification

Product Type RET controller

General Specifications

AISG Output Connector 8-pin DIN Female

AISG Output Connector Quantity 1

Auxiliary Interface USB

Color Gray | Yellow

Dimensions

 Height
 50.8 mm | 2 in

 Width
 127 mm | 5 in

 Depth
 76.2 mm | 3 in

Electrical Specifications

Input Voltage110/240 VacOutput Current at Voltage, continuous3.0 A @ 24 VOutput Current at Voltage, maximum3.0 A @ 24 V

Output Voltage, typical 24 V

Electrical Safety Standard CB | CE | IEC 60950-1

Interface Protocol Signal Data | dc
Power Supply dc Jack

Protocol AISG 1.1 | AISG 2.0

Material Specifications

Material Type Aluminum



ATC200-LITE-USB-EU

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +55 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +131 \,^{\circ}\text{F})$

Relative Humidity Up to 95%, non-condensing

Packaging and Weights

Included Adapter (Europe) | Adapter (United Kingdom) | Control unit | Power

supply | Site configuration worksheet | USB cable

Weight, net 0.4 kg | 0.882 lb

Regulatory Compliance/Certifications

Agency	Classification
CE	Compliant with the relevant CE product directives
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

