

108009424 | M81 BNC-B COUPLER



M81 BNC-B Coupler 50 Ohm

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Multimedia coupler

General Specifications

Application	Module designed for data applications
Mounting	Snap-in

Dimensions

Height	17.526 mm 0.69 in
Width	18.542 mm 0.73 in
Depth	15.24 mm 0.6 in

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	5%–95%, non-condensing

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

