



High-Density Front-Loading Cable Manager, 4U

- Offers bend radius and mechanical protection
- Suitable for Twisted Pair and Fiber Optic patch cords
- Rubber entry/exit retainers ensure cable captivity preventing accidental disturbance of patch cords

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Cable management hardware
Minimum Order Quantity	4
Ordering Note	Sold per piece with an MOQ of 4 pieces

General Specifications

Color	Black
Rack Units	4

Dimensions

Height	177.8 mm 7 in
Width	63.5 mm 2.5 in
Depth	150.114 mm 5.91 in

Material Specifications

Finish	Smooth
Material Type	Galvanized steel PA TPE

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Flammability Rating	UL 94 V-0
Safety Standard	UL cUL

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency**Classification**

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

