

1316MCLICK



Miniature Click-on Hanger for 13–16 mm cable - Hardware Sold Separately

Product Classification

Product Type	Hanger kit
Ordering Note	CommScope® non-standard product

General Specifications

Cables per Hanger	2
Color	Black
Hanger Type	Click-on hanger
Mounting	M8 through hole

Dimensions

Maximum Stack Height	3
Height	38.1 mm 1.5 in
Width	24.9 mm 0.98 in
Length	55.1 mm 2.169 in
Compatible Cable Diameter Range	13–16 mm
Compatible Diameter, maximum	16.3 mm 0.642 in
Compatible Diameter, minimum	13.7 mm 0.539 in
Nominal Size	1/2 in 3/8 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

Mechanical Specifications

Vibration Survival	≥4 hours at resonant frequency
---------------------------	--------------------------------

1316MCLICK

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Environmental Strength Capability	Double cable weight
UV Resistance, minimum with no degradation	≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed	44.7 cm 17.598 in
Width, packed	39.4 cm 15.512 in
Length, packed	17.7 cm 6.969 in
Packaging quantity	10
Weight, gross	0.05 kg 0.11 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power