

# 760251611XYS | 12" Pole Base 4G/5G w/ Fluted Riser Shaft



Round 12 inch diameter, Integrated Pole Base Concealment Pole for 4G /5G deployments, with Straight Fluted riser shaft to house and conceal multiple radios and other wireless infrastructure equipment in the base of the pole.

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole
- Includes everything needed for a low-power 4G/5G outdoor small cell site
- Up to 4 low power radios, integrated AC load center/OVP and Disconnect , PoleTop concealment module for LAA/DBRS radio mounting

Available After Market Kits, ordered separately:

-860668762- AMK-001 for mounting Ericsson 4435 Radio

CommScope Cap H Requires additional Radio Module, ordered separately:

-MTM1029-2000-xx Cap H Radio Module for 12" Integrated Poles

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Integrated pole
<b>Product Brand</b>	Metro Cell
<b>Ordering Note</b>	CommScope® standard product with terms
<b>Warranty</b>	One year

## General Specifications

<b>Antenna Compatibility, CommScope</b>	CommScope Canister Antennas
<b>Antenna Compatibility, Other Vendors</b>	ACE   AMPHENOL   GALTRONICS   GAMMA NU   JMA   KATHREIN   KMW   ROSENBERGER
<b>Antennas Included</b>	None
<b>Color</b>	Light Gray (RAL 7035)
<b>Color Options</b>	Beige-Grey (RAL 7006)   Black (RAL 9005)   Black Green (RAL 6012)   Brown (RAL 8014)   Faux Concrete   Green (RAL 6005)   Metallic Silver   Umbra Grey (RAL 7022)   White (RAL 9010)
<b>Compatible Foundation Type</b>	Poured Concrete   Pre-Cast Concrete
<b>Compatible Smart Devices</b>	WIFI
<b>Cooling</b>	Passive Cooling
<b>Radio Compatibility, CommScope</b>	CAP H

# 760251611XYS | 12" Pole Base 4G/5G w/ Fluted Riser Shaft

---

<b>Radio Compatibility, Ericsson</b>	1281   220x   440x   4435   6701   AIR4435
<b>Radio Compatibility, Nokia</b>	(2) Airscale Micro Radios - LAA & CBRS (Pole Top)   (2) Airscale micro radios – (radio concealment module)   AEUB   AEWB   AHIA   AHIB
<b>Radio Compatibility Samsung</b>	AT1K01   AT1K02   RT2201-46A   RT4401-48A
<b>Radios Included</b>	None

## Dimensions

<b>Height Note</b>	5 ft tall Equipment Base   5.5 ft tall Radio Concealment Module
<b>Pole Height Options</b>	10.668 m   35 ft   6.096 m   20 ft   7.62 m   25 ft   7.925 m   26 ft   9.144 m   30 ft
<b>Width</b>	325.12 mm   12.8 in
<b>Depth</b>	325.12 mm   12.8 in
<b>Depth Note</b>	Round
<b>Pole Diameter</b>	325.12 mm   12.8 in

## Electrical Specifications

<b>Power/Fiber Input</b>	AC load center with OVP and disconnect
--------------------------	--

## Material Specifications

<b>Finish Aluminum</b>	Chromate
<b>Finish Concealment Covers</b>	Powder coated
<b>Material Type</b>	Steel

## Environmental Specifications

<b>Thermal Compliance</b>	GR-487
---------------------------	--------

## \* Footnotes

<b>Warranty</b>	For more information, please consult our Product Warranty guidelines
<b>Pole Height Options</b>	Overall AGL Standard Height