

760033928 | 600G2-1U-UP-FX



G2 1U Fixed Faceplate style, unloaded Fiber Optic Panel, without front faceplate, black

Product Classification

Regional Availability	Asia Australia/New Zealand China India
Regional Availability Note	Discontinued in all other regions since December 14, 2019 and replaced by 760234738 SD-1U-FX-UP in North America, Latin America and EMEA
Portfolio	CommScope®
Product Type	Fiber patch panel

General Specifications

Application	Accepts one G2 front faceplate Accepts two RoloSplices with three trays each
Color	Black
Growth Configuration	Unloaded
Interface, front	Unloaded
Patch Cord Routing	Left sided Right sided
Rack Type	EIA 19 in ETSI 600 mm
Rack Units	1
Shelf Movement	Fixed

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	355.6 mm 14 in

Material Specifications

Finish	Powder coated
Material Type	Steel

Packaging and Weights

Included	Cable management kit Cover Instruction sheet Label Mounting hardware Strain
-----------------	---

relief

Weight, net

3.266 kg | 7.2 lb

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

