

760227306 | UD-2U



Ultra High Density 2U modular cassette sliding Panel, accepts (12)G2 modules or MPO panels, providing up to 144 duplex LC ports or up to 96 MPO ports

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	UD

General Specifications

Application	Accepts twelve G2 modular cassettes
Color	Gray
Intelligence Type	iPatch® ready
Interface, front	Unloaded
Rack Units	2
Shelf Movement	Sliding
Total Ports, quantity	0

Dimensions

Height	88.9 mm 3.5 in
Width	482.6 mm 19 in
Depth	553.97 mm 21.81 in

Material Specifications

Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate (PC) Steel
----------------------	--

Environmental Specifications

Flammability Rating	UL 94 V-0
----------------------------	-----------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Weight, net 9.616 kg | 21.2 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

