

760082560 | RK4P45-36A



Equipment Rack, 4-Post, 36 in (914 mm) D x 7 ft (2134 mm) H - 19 in (482.6 mm) Alu (45U) 12-24 Tapped Rails, Black

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	4 post rack

General Specifications

Color	Black
Rack Type	EIA 19 in
Rack Units	45
Rail Mounting Hole	#12-24

Dimensions

Height	2,133.6 mm 84 in
Channel Width	76.2 mm 3 in
Width	518.16 mm 20.4 in
Depth	1,219.2 mm 48 in
Dimensional Standards	EIA-310-E

Material Specifications

Finish	Powder-coated, textured
Material Type	Aluminum

Mechanical Specifications

Static Load Rating	907.2 kg 2,000.031 lb
---------------------------	-------------------------

Packaging and Weights

Included	Base pan Forty #12-24 x 1/2 in mounting screws Four vertical rack rails Instruction sheet Twenty four 3/8 in split lock washers Twenty four 3/8-16 UNC x 1 in hex head
-----------------	--

760082560 | RK4P45-36A

bolts | Twenty four 3/8-16 hex nuts | Two extruded base angles | Two extruded top angles | Upper plate support

Packaging quantity	1
Packaging Type	Flat packed
Weight, net	44 kg 97.003 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

UK-ROHS

Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant

