

# 760090100 | RK12-52A



Equipment Rack, 2-Post, 12 in (305 mm) Channel x 8ft (2438 mm) H - 19 in (482.6 mm) Alu (52U) 12-24 Tapped Rails, Black

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | 2 post rack   |

## General Specifications

|                           |           |
|---------------------------|-----------|
| <b>Color</b>              | Black     |
| <b>Rack Type</b>          | EIA 19 in |
| <b>Rack Units</b>         | 52        |
| <b>Rail Mounting Hole</b> | #12-24    |

## Dimensions

|                              |                     |
|------------------------------|---------------------|
| <b>Height</b>                | 2,438.4 mm   96 in  |
| <b>Channel Width</b>         | 304.8 mm   12 in    |
| <b>Width</b>                 | 518.16 mm   20.4 in |
| <b>Depth</b>                 | 609.6 mm   24 in    |
| <b>Dimensional Standards</b> | EIA-310-E           |

## Material Specifications

|                      |                         |
|----------------------|-------------------------|
| <b>Finish</b>        | Powder-coated, textured |
| <b>Material Type</b> | Aluminum                |

## Mechanical Specifications

|                           |                         |
|---------------------------|-------------------------|
| <b>Static Load Rating</b> | 453.6 kg   1,000.016 lb |
|---------------------------|-------------------------|

## Packaging and Weights

|                 |   |
|-----------------|---|
| <b>Included</b> | Forty #12-24 x 1/2 in mounting screws   Instruction sheet   Twelve 3/8 in split lock washers   Twelve 3/8-16 UNC x 1 in hex head bolts   Twelve 3/8-16 hex nuts   Two extruded base |
|-----------------|---|

# 760090100 | RK12-52A

---

angles | Two extruded top angles | Two vertical rack rails

|                           |                      |
|---------------------------|----------------------|
| <b>Packaging quantity</b> | 1                    |
| <b>Packaging Type</b>     | Flat packed          |
| <b>Weight, net</b>        | 27.67 kg   61.002 lb |

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |

