



Unshielded Discrete Distribution Module Panel, SL, 2U, 48 port, Black

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	RJ45 patch panel
<b>Product Series</b>	SL Series

## General Specifications

<b>Cable Type</b>	Unshielded
<b>Color</b>	Black
<b>Modules, quantity</b>	0
<b>Panel Style</b>	Straight
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	2
<b>Total Ports, quantity</b>	48

## Dimensions

<b>Height</b>	88.9 mm   3.5 in
<b>Width</b>	482.6 mm   19 in
<b>Depth, with cable management</b>	119.38 mm   4.7 in

## Material Specifications

<b>Material Type</b>	High-impact, flame retardant, thermoplastic   Powder-coated steel
----------------------	---

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Flammability Rating</b>	UL 94 V-0

# 760237041 | CPP-UDDM-SL-2U-48

---

**Safety Standard** RCM | UL | cUL

## Packaging and Weights

**Packaging Material** Eco-friendly, single-use plastics-free

**Packaging quantity** 1

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

