

PFP-PX-8M

Power Express module, connects up to 8 Powered Fiber Cables



Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type

Power supply module

Dimensions

Height

43.688 mm | 1.72 in

Width

87.376 mm | 3.44 in

Depth

193.675 mm | 7.625 in

Compatible Gauge Range

24–8 AWG

Electrical Specifications

Input Current Range

0–20 A

Input Voltage Range

-42 to -60 Vdc

Output Voltage Range

-42 to -58 Vdc

Output Voltage, nominal

-57 Vdc

Electrical Safety Standard

CSA C22.2 No. 60950-1-03

Electromagnetic Compatibility/Interference (EMC/EMI)

FCC-CFR, Part 15, sub-part B | GR1089 Class A

Total Output Power

100 W, per circuit

Environmental Specifications

Operating Temperature

-40 °C to +65 °C (-40 °F to +149 °F)

Relative Humidity

5%–95%, non-condensing

Standards Compliance

EN 61000-4-2 level 4

PFP-PX-8M

Packaging and Weights

Packaging quantity	1
Packaging Type	Carton
Weight, net	0.363 kg 0.8 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

