## PFP-SPS-1600M



#### Slimline SPS DC Rectifier Module, 1600 Watts

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin

America | North America

**Product Type** Power supply module

**Dimensions** 

 Height
 41.656 mm | 1.64 in

 Width
 126.492 mm | 4.98 in

 Depth
 205.994 mm | 8.11 in

**Electrical Specifications** 

**Input Current Range** 15-12A @ 90-120Vac | 7.5A @ 230Vac

Output Voltage Range -42 to -58 Vdc

Electrical Safety Standard CE | CSA C22.2 No. 60950-1-03 | UL

Electromagnetic Compatibility/Interference (EMC/EMI) FCC-CFR, Part 15, sub-part B | GR1089 Class A

Power Efficiency 95 %

**Environmental Specifications** 

**Operating Temperature** -40 °C to +75 °C (-40 °F to +167 °F)

Standards Compliance EN 61000-4-2 level 4 | GR 1089, Issue 4 | GR-63

Packaging and Weights

Packaging quantity 1

Packaging Type Carton

**Weight, net** 1.397 kg | 3.08 lb

**COMMSCOPE®** 

# PFP-SPS-1600M

### Regulatory Compliance/Certifications

Agency C	lassification
----------	---------------

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

