


FE-14126-E



HELIAX® Excess Fiber Junction Box kit includes 5' of flexible conduit and a NPT fitting, excess storage capacity of 100 ft

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Outdoor junction box
Product Brand	HELIAX®

General Specifications

Color	Gray
Fiber System Configuration Type	Hybrid with OVP, low inductance, 6 RRU
Mounting	Pipe, 76.2 mm (3 in) OD Wall

Dimensions

Height	304.8 mm 12 in
Width	355.6 mm 14 in
Depth	152.4 mm 6 in

Material Specifications

Material Type	High-impact polycarbonate, UV resistant
----------------------	---

Environmental Specifications

Operating Temperature	-40 °C to +75 °C (-40 °F to +167 °F)
Environmental Space	Indoor Outdoor

Packaging and Weights

Included	Mounting kit
Weight, net	1.996 kg 4.4 lb

Regulatory Compliance/Certifications

FE-14126-E

Agency**Classification**

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

