T-25-UW-43-M



Termination Load, 0–6000 MHz

Product Classification	
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Termination Load
General Specifications	
Device Type	Termination Load
Application	Indoor/Outdoor
Color	Black
Inner Contact Plating	Silver
Interface	4.3-10 Male
Outer Contact Plating	Trimetal
Dimensions	
Length	81 mm 3.189 in
Diameter, maximum	35 mm 1.378 in
Electrical Specifications	
Average Power, maximum	25 W
Impedance	50 ohm
Operating Frequency Band	0 – 6000 MHz
VSWR	1.15
Environmental Specifications	

Operating Temperature-35 °C to +50 °C (-31 °F to +122 °F)Relative HumidityUp to 100%Ingress Protection Test MethodIEC 60529:2001, IP65

Packaging and Weights

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 26, 2024



T-25-UW-43-M

Height, packed	98 mm 3.858 in
Width, packed	53 mm 2.087 in
Length, packed	58 mm 2.283 in
Weight, gross	0.2 kg 0.441 lb
Weight, net	0.18 kg 0.397 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 26, 2024

