



AMP STACK™ III Connector Splice Kit, pre-sealed, 25-pair

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Product Type | Connector kit |
| Product Brand | AMP STACK™ |
| Product Series | AMP STACK |
| Ordering Note | Minimum order quantity, 120 parts |

General Specifications

| | |
|--------------------------------|--------------------------|
| Color | Gold ivory Transparent |
| Connector Sealant | Gel filled |
| Connector Splicing Type | Straight (In-line) |
| Pairs, quantity | 25 |

Dimensions

| | |
|---|--------------------|
| Compatible Insulated Conductor Diameter, maximum | 1.65 mm 0.065 in |
| Compatible Conductor Gauge, solid | 28–20 AWG |

Material Specifications

| | |
|---------------------------------|----------------------------|
| Contact Base Material | Phosphor Bronze |
| Contact Plating Material | Tin |
| Material Type | Glass filled polycarbonate |

Environmental Specifications

| | |
|----------------------------|---------|
| Environmental Space | Outdoor |
|----------------------------|---------|

9-737830-2 | AS-25-Splice-Filled

Packaging and Weights

| | |
|---------------------------|------------------|
| Included | Base with covers |
| Packaging quantity | 12 |
| Packaging Type | Bag Box |