

HFDC-48FIBER



HELIAX® Fiber Distribution Closure 48 fibers - 24 DLCs UPC.

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Outdoor junction box
Product Brand	HELIAX®

General Specifications

Application	Used as a fiber junction box
Total Fiber Adapters	24
Color	Black
Door, quantity	2
Mounting	Pipe, 44–114 mm (1.75–4.5 in) OD
Total Fibers, quantity	48
Total Ports, quantity	12

Dimensions

Height	369.976 mm 14.566 in
Width	213.995 mm 8.425 in
Depth	117.983 mm 4.645 in
Jumper Breakout Length, Maximum	85 mm 3.346 in
Jumper Outlet, Quantity, Maximum	24
Jumper Outlet Diameter, Minimum	0 mm 0 in
Jumper Outlet Diameter, Maximum	5.5 mm 0.217 in
Trunk Entry, Diameter, Maximum	17.5 mm 0.689 in
Trunk Entry, Quantity, Maximum	4

Material Specifications

Material Type	High-impact polycarbonate, UV resistant
----------------------	---

HFDC-48FIBER

Mechanical Specifications

Impact Test Method EN62262 | IEC62262: IK07

Environmental Specifications

Operating Temperature -40 °C to +75 °C (-40 °F to +167 °F)

Environmental Space Outdoor

Qualification Standards IEC 60529, IP68

Packaging and Weights

Included Mounting kit

Weight, net 3.946 kg | 8.7 lb