

## SYSTIMAX 360™ iPatch® 1100GS3 Evolve U/UTP Patch Panel, 24 port



### Product Classification

#### Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

#### Portfolio

SYSTIMAX®

#### Product Type

RJ45 patch panel

#### Product Brand

SYSTIMAX 360™ | iPatch®

### General Specifications

#### ANSI/TIA Category

6

#### Cable Type

Unshielded

#### Color

Silver

#### Intelligence Type

iPatch® enabled

#### Panel Style

Straight

#### Rack Units

1

#### Total Ports, quantity

24

#### Wiring

T568A | T568B

### Dimensions

#### Height

44.45 mm | 1.75 in

#### Width

482.6 mm | 19 in

#### Depth

206.5 mm | 8.13 in

#### Compatible Diameter Over Dielectric, maximum

1.168 mm | 0.046 in

### Electrical Specifications

#### Current Rating at Temperature

1.5 A @ 20 °C | 1.5 A @ 68 °F

#### Dielectric Withstand Voltage, RMS, conductive surface

1,500 Vac @ 60 Hz

#### Insulation Resistance, minimum

500 MOhm

## Mechanical Specifications

**Plug Insertion Life, minimum** 750 times

## Environmental Specifications

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Safety Standard** UL | cUL

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

