CHD-2U-W



SYSTIMAX® CHD 2U sliding tray fiber panel, accepts (24) CHD ULL modules, splice cassettes or MPO panels, providing up to 144 duplex LC ports or up to 144 MPO ports, white, High Speed Migration

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type

CommScope®

Fiber patch panel

Product Series CHD

General Specifications

Application Accepts 24 CHD Universal Modules, or CHD MPO/LC adapter packs

Color White
Interface, front Unloaded

Rack Units 2

Shelf Movement Sliding

Total Ports, quantity 0

Dimensions

 Height
 88.9 mm | 3.5 in

 Width
 482.6 mm | 19 in

 Depth
 538.48 mm | 21.2 in

Packaging and Weights

Weight, net 8.8 kg | 19.4 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

Page 1 of 2



CHD-2U-W

UK-ROHS

Compliant

