EHD-4U



SYSTIMAX® EHD 4U sliding tray fiber panel, accepts (24) EHD ULL modules, splice cassettes or MPO panels, providing up to 288 duplex LC ports or up to 288 MPO ports, High Speed Migration

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber patch panel

Product Series EHD

General Specifications

Application Accepts 24 EHD Universal Modules, or EHD MPO adapter packs

Color Black

Interface, front Unloaded

Rack Units 4

Shelf Movement Sliding

Total Ports, quantity 0

Dimensions

 Height
 177.8 mm | 7 in

 Width
 482.6 mm | 19 in

 Depth
 538.48 mm | 21.2 in

Packaging and Weights

Weight, net 15.604 kg | 34.4 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

Page 1 of 2



EHD-4U



