

# 860662430 | Round Straight 8.625" Ladder Height Ports



8.625" diameter pole that accomodates ladder height enclosure installation

Metal pole that supports a variety of installation methods such as poured concrete, embedded pole, pre-cast, and helical foundations  
Break Away Compatible  
Enclosure mounting ports at 10' AGL  
Configurable color and pole height

Foundation Kit Ordered Separately

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Standard poles
<b>Product Brand</b>	Metro Cell
<b>Ordering Note</b>	CommScope® standard product with terms
<b>Warranty</b>	One year

## General Specifications

<b>Color</b>	Galvanized
<b>Color Options</b>	Antique Bronze (SRSL 45893)   Beige-Grey (RAL 7006)   Black (RAL 9005)   Black Green (RAL 6012)   Brown (RAL 8014)   Fairfax Brown (SW 2856)   Faux Concrete   Federal Park Brown   Green (RAL 6005)   Light Gray (RAL 7035)   Metallic Silver   Umbra Grey (RAL 7022)   White (RAL 9010)
<b>Compatible Foundation Type</b>	Embedded Pole   Embedded with Foam   Helical Anchor   Poured Concrete   Pre-Cast Concrete   Split Helical Anchors
<b>Compatible Smart Devices</b>	Cameras   Digital Signage   Emergency Call Station   Environmental Monitoring   Security Lighting   WIFI

## Dimensions

<b>Pole Height Options</b>	11.278 m   37 ft   9.754 m   32 ft
<b>Width</b>	219.075 mm   8.625 in
<b>Luminaire Mount Height</b>	7.315 m   24 ft
<b>Mounting Bolt Circle Diameter</b>	406.4 mm   16 in

# 860662430 | Round Straight 8.625" Ladder Height Ports

## Ordering Tree



## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Galvanized steel

## \* Footnotes

<b>Warranty</b>	For more information, please consult our Product Warranty guidelines
<b>Pole Height Options</b>	Overall AGL Standard Height