## 760187187 | 360-E-MOD-1U-24



#### SYSTIMAX 360™ Evolve 24-port flat panel

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin

America | North America

Portfolio SYSTIMAX®

Product Type RJ45 patch panel

Product Brand SYSTIMAX 360™

Product Series M Series

General Specifications

Cable Type Unshielded

**Color** Cool gray

Modules, quantity 24

Panel StyleStraightRack TypeEIA 19 in

Rack Units 1

Total Ports, quantity 24

**Wiring** T568A | T568B

**Dimensions** 

**Height** 44.45 mm | 1.75 in

**Label Height** 10.922 mm | 0.43 in

**Width** 482.6 mm | 19 in

**Depth** 40.64 mm | 1.6 in

**Depth, with cable management** 170.18 mm | 6.7 in

**Label Length** 33.782 mm | 1.33 in

Compatible Diameter Over Dielectric, maximum 1.168 mm | 0.046 in

**Compatible Diameter Over Dielectric, minimum** 0.762 mm | 0.03 in



# 760187187 | 360-E-MOD-1U-24

### **Electrical Specifications**

Current Rating at Temperature 1.5 A @ 20 °C | 1.5 A @ 68 °F

Dielectric Withstand Voltage, RMS, conductive surface1,500 Vac @ 60 HzDielectric Withstand Voltage, RMS, contact-to-contact1,000 Vac @ 60 Hz

**Insulation Resistance, minimum** 500 MOhm

Material Specifications

Material Type High-impact, flame retardant, thermoplastic | Powder-

coated steel

**Environmental Specifications** 

**Operating Temperature**  $-10 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (+14  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

**Relative Humidity**Up to 95%, non-condensing

Flammability Rating UL 94 V-0
Safety Standard UL | cUL

Packaging and Weights

Packaging Material Eco-friendly, single-use plastics-free

Packaging quantity 1

**Weight, net** 0.499 kg | 1.1 lb

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



