

# 760239077 | UDS-2U-WH-LC-B-ULL

---



UDS 2RU splice panel, 144 duplex LC/UPC ports, Enhanced Method B, ULL

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch/splice panel
<b>Product Series</b>	UDS

## General Specifications

<b>Application</b>	Preloaded with 12 UDS modules
<b>Color</b>	White
<b>Intelligence Type</b>	Not iPatch® ready
<b>Interface, front</b>	LC/UPC
<b>Pigtail Assembly Type</b>	12-fiber, ribbon
<b>Pigtails Included, quantity</b>	12
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	2
<b>Shelf Movement</b>	Sliding, rear
<b>Splice Trays Included, quantity</b>	4

## Dimensions

<b>Height</b>	88.9 mm   3.5 in
<b>Width</b>	444.5 mm   17.5 in
<b>Depth</b>	609.6 mm   24 in

## Optical Specifications

<b>Insertion Loss, maximum</b>	0.25 dB
--------------------------------	---------

## Environmental Specifications

**Safety Standard** cUL US 1863

## Packaging and Weights

**Packaging quantity** 1

**Weight, net** 6.804 kg | 15 lb

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Above maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant/Exempted

UK-ROHS

Compliant

