DFJ-2M5A-TM

HELIAX® Discrete, 2 multimode fiber, 5 mm LSZH cable. End 1: DLC 12" breakout. End 2: DLC 12" breakout



Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Wireless Fiber Cable Assemblies

Product Brand HELIAX®
Product Series DFJ

Ordering Note CommScope® non-standard product

General Specifications

Construction Type Discrete fiber tail

 Interface, Connector A
 DLC

 Interface, Connector B
 DLC

 Jacket Color
 Black

 Total Fibers, quantity
 2

Dimensions


Cable Assembly Length Range (m) 5-50

Diameter Over Jacket 4.8 mm | 0.189 in

Ordering Tree



DFJ-2M5A-TM



Material Specifications

Jacket Material Low Smoke Zero Halogen (LSZH)

Optical Specifications

Fiber Type OM2, bend insensitive

Insertion Loss, typical note Insertion loss is measured at 850 nm

Insertion Loss, typical 0.5

Environmental Specifications

Operating Temperature -40 °C to +80 °C (-40 °F to +176 °F)

Environmental Space Low Smoke Zero Halogen (LSZH)

Packaging and Weights

Cable weight 25 kg/km | 16.799 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



* Footnotes



DFJ-2M5A-TM

Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)

