

DFP-2SLC01



HELIAX® Pigtail, 2 single mode fiber, 6 mm cable, DLC

Product Classification

Regional Availability	Asia
Portfolio	CommScope®
Product Type	Wireless Fiber Cable Assemblies
Product Brand	HELIAX®
Product Series	DFJ
Ordering Note	CommScope® non-standard product

General Specifications


Construction Type	Discrete fiber tail
Interface, Connector A	DLC
Interface Body Style, connector A	Straight
Interface, Connector B	DLC
Interface Feature, connector B	Standard
Jacket Color	Black
Total Fibers, quantity	2

Dimensions

Cable Assembly Length Range (ft)	5 – 300
Diameter Over Jacket	6 mm 0.236 in

Ordering Tree

DFP-2SLC01



Optical Specifications

Fiber Type	G.657.A2
Insertion Loss, typical note	Insertion loss is measured at 1310 and 1550 nm
Insertion Loss, typical	0.5

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space	Outdoor

Packaging and Weights

Cable weight	24.9 kg/km 16.732 lb/kft
---------------------	----------------------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



DFP-2SLC01

* Footnotes

Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)