

# C100-BNFSR-2M

---



## Product Classification

<b>Product Type</b>	Braided cable assembly
<b>Product Brand</b>	CNT®
<b>Product Series</b>	CNT-100

## General Specifications

<b>Body Style, Connector A</b>	Bulkhead
<b>Body Style, Connector B</b>	Right angle
<b>Cable Family</b>	CNT-100
<b>Interface, Connector A</b>	N Female
<b>Interface, Connector B</b>	SMA Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	2 m   6.562 ft
<b>Nominal Size</b>	0.100 in

## VSWR/Return Loss

<b>Frequency Band</b>	<b>VSWR</b>	<b>Return Loss (dB)</b>
<b>700–3000 MHz</b>	1.329	17

## Jumper Assembly Sample Label

# C100-BNFSR-2M

---



## Included Products

- CNT-100-FR    –    CNT-100-FR, CNT<sup>®</sup> 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant polyolefin jacket