F1-HMHM-3M-W-D



D-CLASS FSJ1-50A SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male with HELIAX® SureGuard weatherproofing boot , 3 m

WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type SureFlex® D-CLASS, dynamic PIM

Product Brand HELIAX® | SureFlex®

Product Series FSJ1-50A

General Specifications

Body Style, Connector AStraightBody Style, Connector BStraightInterface, Connector A4.3-10 MaleInterface, Connector B4.3-10 Male

Specification Sheet Revision Level

Dimensions

Length 3 m | 9.843 ft

Nominal Size 1/4 in

Logo Image



F1-HMHM-3M-W-D



Electrical Specifications

3rd Order IMD Dynamic -119 dBm

3rd Order IMD Dynamic Test MethodTwo +43 dBm carriers per IEC 62037

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698-960 MHz	1.152	23.02
1700-2200 MHz	1.152	23.02
2500-2700 MHz	1.152	23.02

Jumper Assembly Sample Label



F1-HMHM-3M-W-D



Environmental Specifications

Immersion Test MethodMeets IEC 60529:2001, IP68 in mated condition

Weatherproofing Method HELIAX® SureGuard weatherproofing boot

Packaging and Weights

Included Weatherproofing boot

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system