

FJ-2SM-015-0.75M



HELIAX® Ruggedized, Bend Insensitive Singlemode Fiber, DLC to DLC
Fiber Distribution Cable, 0.75 m

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Wireless Fiber Cable Assemblies
Product Series	FJ
Ordering Note	CommScope® non-standard product

General Specifications

Construction Type	Direct fiber tail
Interface, Connector A	DLC
Interface Body Style, connector A	Straight
Interface, Connector B	DLC
Interface Body Style, connector B	Straight
Jacket Color	Black
Total Fibers, quantity	2

Dimensions

Cord Length	0.75 m 2.461 ft
Diameter Over Jacket	6 mm 0.236 in

Mechanical Specifications

Minimum Bend Radius, furcation	30 mm 1.181 in
---------------------------------------	------------------

Optical Specifications

Fiber Type	G.657.A2
Insertion Loss, typical note	Insertion loss is measured at 1310 and 1550 nm
Insertion Loss, typical	0.5

FJ-2SM-015-0.75M

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Environmental Space Indoor

Packaging and Weights

Cable weight 37.1 kg/km | 24.93 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)