SA-3C



PIM-free, Three-way Snap-in Stand-off Adapter. Two sets of slots for round member attachment. 3/8" holes for bolt down attachment. Three 3 /4" holes for Snap-in style hangers

Product Classification

Product Type Adapter
Product Brand PIM-Guard

Ordering Note CommScope® standard product (Global)

General Specifications

Adapter Type Stand-off adapter

Color Black

Mounting 3/4 in through hole | 3/8 in through hole | Round member

Dimensions

 Height
 36.322 mm | 1.43 in

 Outside Width
 40.132 mm | 1.58 in

 Outside Length
 87.122 mm | 3.43 in

Material Specifications

Material Type Engineered plastic

Mechanical Specifications

Maximum Loading Triple stack for hangers SSH-47, SSH-710, SSH-1014, SSH-1416, SSH-411,

SSH-1117

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Environmental Strength Capability Double cable weight

UV Resistance, minimum with no degradation ≥1000 hours

Packaging and Weights

COMMSCOPE®

SA-3C

 Height, packed
 17 cm | 6.693 in

 Width, packed
 13 cm | 5.118 in

 Length, packed
 10 cm | 3.937 in

Packaging quantity 10

Weight, gross 0.27 kg | 0.595 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

