




NOTES:

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	ECR 8000036448: REL TO PRODUCTION PER EAO 607060.	25JUL19 RDD	CC/P.J
B	ECR 8000036739: UPDATE DRAWING WITH LATEST MODEL.	14AUG19 RFF	CC/P.J
C	ECR 8000038038: UPDATE DRAWING.	4NOV19 LJ	S.LIU/HANSEN.W
D	ECR 8000040178: UPDATE DRAWING.	9APR20 Q.W	CC/ZT
E	ECR 8000042182: UPDATE DRAWING.	26AUG20 LJ	WXW/ZT



AEKT

**COMMScope, INC. OF NORTH CAROLINA**

TOLERANCES		SAP MATERIAL MASTER	
0 PLACE X ±	2 PLACE .XX ±		
1 PLACE .X ±	ANGLES ±		
FINISH		MATERIAL	

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS INTERPRET PER ISO STANDARDS HANDBOOK TECHNICAL DRAWINGS VOLUMES 1 & 2, THIRD EDITION (2002)	NAME	DATE	TITLE <b>PRODUCT DRAWING</b>	
	CE RDD	25JUL19		
	RW JL1132	08/27/2020		
	RV XW1038	08/27/2020		
	AD TZ1021	08/27/2020		
RE ZHHCHEN	08/27/2020			
ECN 8000042182-O			SCALE	DOCUMENT NO.
			<b>1:5</b>	<b>AEKT-L</b>

DENSITY	g/mm <sup>3</sup>		
MASS	grams		
VOLUME	mm <sup>3</sup>		
SURFACE AREA	mm <sup>2</sup>		
HEIGHT		SIZE	WORK AREA 23
LENGTH		MODEL	
WIDTH		DRAWING	
		<b>A2</b>	
		VERSION	STATUS
		04	RE
		REVISION	VERSION
		E	04
		REVISION	STATUS
		E	RE
		REVISION	REVISION
		E	E
		SHEET	
		1 OF 1	