

# 1671495-1

---



## High-Density Front-Loading Cable Manager, 1U

- Offers bend radius and mechanical protection
- Suitable for Twisted Pair and Fiber Optic patch cords
- Rubber entry/exit retainers ensure cable captivity preventing accidental disturbance of patch cords

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Cable management hardware
<b>Minimum Order Quantity</b>	16
<b>Ordering Note</b>	Sold per piece with an MOQ of 16 pieces

## General Specifications

<b>Color</b>	Black
<b>Rack Units</b>	1

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	63.5 mm   2.5 in
<b>Depth</b>	150.114 mm   5.91 in

## Material Specifications

<b>Finish</b>	Smooth
<b>Material Type</b>	Galvanized steel   PA   TPE

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	UL   cUL

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

