

# FGS-MTRM-2B-IMP

---



FiberGuide® Trumpet Flare for Dual Drop Downspout with Divider (FGS-MDSP-2B-IMP), 4x6in, Yellow

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Trumpet flare   |
| <b>Product Brand</b>         | FiberGuide®   |
| <b>Product Series</b>        | FGS   |

## General Specifications


|                     |               |
|---------------------|---------------|
| <b>Color</b>        | Yellow        |
| <b>Orientation</b>  | Vertical      |
| <b>Section Type</b> | Trumpet flare |

## Dimensions

|                          |                               |
|--------------------------|-------------------------------|
| <b>Height</b>            | 50.8 mm   2 in                |
| <b>Width</b>             | 144.526 mm   5.69 in          |
| <b>Length</b>            | 261.874 mm   10.31 in         |
| <b>System Dimensions</b> | 102 mm x 152 mm (4 in x 6 in) |

## Ordering Tree

# FGS-MTRM-2B-IMP



## Section Color

|   |       |        |
|---|-------|--------|
| 9 | empty | yellow |
|   | B     | black  |

## Section Size

|    |                   |   |
|----|-------------------|---|
| 10 | 2A                | 4 x 6 in, for dual downspout              |
|    | 2B-IMP            | 4 x 6 in, for dual downspout with divider |
|    | A                 | 4 x 4 in                                  |
|    | B                 | 4 x 6 in                                  |
|    | C                 | 2 x 2 in                                  |
|    | D                 | 4 x 4 in, vertical                        |
|    | DS                | 2 x 4 in, vertical                        |
|    | E                 | 2 x 4 in, vertical , black*               |
|    | F                 | 4 x 12 in                                 |
|    | G                 | 2 x 6 in                                  |
| H  | 4 x 24 in, black* |   |

\* Only comes in black

## Material Specifications

**Material Type** Engineering Thermoplastic

## Environmental Specifications

**Flammability Rating** CSA S143 | UL 2024 | UL 94 V-0

**Halogen Characteristics** Blue Angel | TCO '99 | WEEE

**Safety Standard** CSA | UL

## Packaging and Weights

**Included** Hardware

**Packaging quantity** 2

## Regulatory Compliance/Certifications

| Agency     | Classification   |
|------------|--|
| CHINA-ROHS | Below maximum concentration value  |
| REACH-SVHC | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS       | Compliant  |
| UK-ROHS    | Compliant  |



