

24312A



Lace-up Hoisting Grip for 1-5/8 in coaxial cable and elliptical waveguide
44, 52, and 63

Product Classification

Product Type	Hoisting grip
Ordering Note	CommScope® standard product (Global)

General Specifications

Attachment Spacing Intervals	60.96 m 200 ft
Hoisting Grip Type	Lace-up hoisting grip
Support Clamp	Not included
Tool Type	Hoisting grip

Dimensions

Grip Length, minimum	685.8 mm 27 in
Leader Length, minimum	304.8 mm 12 in
Nominal Size	1-5/8 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Mechanical Specifications

Pull Load Capacity	430.913 kg 950 lb
---------------------------	---------------------

Packaging and Weights

Height, packed	38.1 mm 1.5 in
Width, packed	223.52 mm 8.8 in

24312A

Length, packed	238.76 mm 9.4 in
Packaging quantity	1
Weight, gross	0.4 kg 0.882 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

