



Single Entrance Panel for elliptical waveguide 64

Product Classification

Product Type Entrance panel

General Specifications

Color Gray

Entry Panel Port Size 101.6 mm | 4 in

Number of Ports 1

Panel Type Single

Dimensions

Height 76.2 mm | 3 in

Width 127 mm | 5 in

Waveguide Size WR137 | WG14 | R70

Material Specifications

Material Type Aluminum

Environmental Specifications

Weather Resistance Test Method 04AS00-03.9.0 | IEC 60529.14.2

Packaging and Weights

Height, packed 279.4 mm | 11 in

Width, packed 203.2 mm | 8 in

Length, packed 165.1 mm | 6.5 in

Included Boot | Plate

245314-64

Packaging quantity 1
Weight, gross 1.25 kg | 2.756 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system



Included Products

- 204673-1 – 1 Port Entrance Panel 1 x 1
- WGB4-64 – Boot Assembly, 4 in, for elliptical waveguide 64