



Messenger Wire Tie Wrap with spacer for RCT RADIAX® Radiating cable

- For added support, use with Andrew Stainless Steel Cable Ties (250058) at 5 meter intervals

Product Classification

Product Type Wire tie

General Specifications

Cables per Hanger 1

Color Black

Hanger Type Cable tie

Mounting Messenger wire

Dimensions

Height 25.4 mm | 1 in

Width 12.7 mm | 0.5 in

Length 405.9 mm | 15.98 in

Compatible Diameter, maximum 114 mm | 4.488 in

Nominal Size 1-1/4 in | 1-5/8 in | 1/2 in | 7/8 in

Material Specifications

Material Type Engineered plastic

Mechanical Specifications

Pullout Force, maximum with no cable slippage 445 N | 100.04 lbf

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Flammability Test Method UL 94-HB

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

250062

Packaging quantity 1
Weight, gross 0.02 kg | 0.044 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

