

Lace-up Hoisting Grip for 1-1/4 in coaxial cable and elliptical waveguide 64



Product Classification

Product Type	Hoisting grip
Ordering Note	CommScope® non-standard product

General Specifications

Attachment Spacing Intervals	60.96 m 200 ft
Hoisting Grip Type	Lace-up hoisting grip
Support Clamp	Not included
Tool Type	Hoisting grip

Dimensions

Grip Length, minimum	635 mm 25 in
Leader Length, minimum	203.2 mm 8 in
Nominal Size	1-1/4 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Mechanical Specifications

Pull Load Capacity	408.233 kg 900 lb
---------------------------	---------------------

Packaging and Weights

29961

Height, packed	55.88 mm 2.2 in
Width, packed	236.22 mm 9.3 in
Length, packed	236.22 mm 9.3 in
Packaging quantity	1
Weight, gross	0.38 kg 0.838 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

REACH-SVHC

ROHS

UK-ROHS

Classification

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant

