

CK4652-000 | FIST-FCASA2-8M471NN-L



FIST® Fiber Splice Tray with Field Installable CWDM, 8 Channels, Multiplexing, 1471nm starting wavelength, 20nm channel spacing, all fibers at left side

Product Classification

| | |
|------------------------------|------------------|
| Regional Availability | EMEA |
| Product Type | CWDM splice tray |
| Product Brand | FIST® |
| Product Series | FIST-FCASA2 |

General Specifications

| | |
|--------------------------|--|
| Application | For use with FIST fiber splice closures For use with FIST panels |
| Interface, Input | Stub tail |
| Interface, Output | Stub tail |

Packaging and Weights

| | |
|---------------------------|---|
| Packaging quantity | 1 |
|---------------------------|---|

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|---|
| CHINA-ROHS | Above maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

