

# FA-2628-SIH

---



## Snap-In Hanger and Grommet kit for HELIAX® Cables, 26-28mm

### Product Classification

<b>Product Type</b>	Hanger kit
<b>Ordering Note</b>	CommScope® non-standard product

### General Specifications

<b>Cables per Hanger</b>	1
<b>Color</b>	Black   Silver
<b>Hanger Type</b>	Hanger kits
<b>Mounting</b>	3/8 in (M10) drilled cable ladder

### Dimensions

<b>Maximum Stack Height</b>	3
<b>Height</b>	58.9 mm   2.319 in
<b>Width</b>	38.1 mm   1.5 in
<b>Length</b>	76.2 mm   3 in
<b>Compatible Cable Diameter Range</b>	26–28 mm
<b>Compatible Diameter, maximum</b>	28 mm   1.102 in
<b>Compatible Diameter, minimum</b>	26 mm   1.024 in
<b>Nominal Size</b>	1-1/4 in

### Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

### Material Specifications

<b>Material Type</b>	EPDM rubber   Stainless steel
----------------------	-------------------------------

### Mechanical Specifications

# FA-2628-SIH

---

## Vibration Survival

≥4 hours at resonant frequency

## Environmental Specifications

### Operating Temperature

-40 °C to +85 °C (-40 °F to +185 °F)

### Corrosion Resistance, minimum with no degradation

≥500 hours in salt spray chamber

### Environmental Strength Capability

Double cable weight

## Packaging and Weights

### Height, packed

26 cm | 10.236 in

### Width, packed

9 cm | 3.543 in

### Length, packed

9 cm | 3.543 in

### Packaging quantity

10

### Weight, gross

0.53 kg | 1.168 lb

## Regulatory Compliance/Certifications

### Agency

### Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power