860641110 | Round Straight 8.625" Diameter with 24' Lum mount

8.625" diameter pole that accomodates Small Cell equipment and Smart City devices

Metal pole that supports a variety of installation methods such as poured concrete, embedded pole, pre-cast, and helical foundations Break Away Compatible

Configurable color and pole height

22' and 25' Poles do not have luminaire mounts

Foundation Kit Ordered Separately

Product Classification

PortfolioCommScope®Product TypeStandard polesProduct BrandMetro Cell

Ordering Note CommScope® standard product with terms

Warranty One year

General Specifications

Color Galvanized

Color Options Antique Bronze (SRSL 45893) | Beige-Grey (RAL 7006) | Black (RAL 9005) | Black Green

(RAL 6012) | Brown (RAL 8014) | Fairfax Brown (SW 2856) | Faux Concrete | Federal Park Brown | Green (RAL 6005) | Light Gray (RAL 7035) | Metallic Silver | Signal Black

(RAL 9004) | Umbra Grey (RAL 7022) | White (RAL 9010)

Compatible Foundation Type Embedded Pole | Embedded with Foam | Helical Anchor | Poured Concrete | Pre-Cast

Concrete | Split Helical Anchors

Compatible Smart Devices Cameras | Digital Signage | Emergency Call Station | Environmental

Monitoring | Security Lighting | WIFI

Dimensions

Pole Height Options 11.278 m | 37 ft | 12.192 m | 40 ft | 6.706 m | 22 ft | 7.62 m | 25 ft | 8.23

m | 27 ft | 8.534 m | 28 ft | 9.144 m | 30 ft | 9.754 m | 32 ft

Width 219.075 mm | 8.625 in


Luminaire Mount Height 7.315 m | 24 ft

Mounting Bolt Circle Diameter 406.4 mm | 16 in

Ordering Tree

COMMSC PE®

860641110 | Round Straight 8.625" Diameter with 24' Lum mount



Material Specifications

Finish Powder coated

Material Type Galvanized steel

* Footnotes

Warranty For more information, please consult our Product Warranty guidelines

Pole Height Options Overall AGL Standard Height