


# 1499418-2 | 1061F SLT C5E 25/24 U/UTP R1000



1061F Cat5e U/UTP Cable, Riser, Slate Jacket, 25 pair count, 1000 ft (305 M) length reel

## Product Classification

<b>Regional Availability</b>	Asia   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Twisted pair cable

## General Specifications

<b>Product Number</b>	1061F
<b>ANSI/TIA Category</b>	5e
<b>Cable Component Type</b>	Horizontal
<b>Cable Type</b>	U/UTP (unshielded)
<b>Conductor Type, singles</b>	Solid
<b>Conductors, quantity</b>	50
<b>Jacket Color</b>	Slate
<b>Pairs, quantity</b>	25
<b>Transmission Standards</b>	ANSI/TIA-568.2-D   CENELEC EN 50288-6-1   ISO/IEC 11801 Class D

## Dimensions

<b>Cable Length</b>	304.8 m   1000 ft
<b>Diameter Over Jacket, nominal</b>	12.7 mm   0.5 in
<b>Conductor Gauge, singles</b>	24 AWG

## Electrical Specifications

<b>Operating Voltage, maximum</b>	80 V
<b>Remote Powering</b>	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A

# 1499418-2 | 1061F SLT C5E 25/24 U/UTP R1000

---

**Safety Voltage Rating** 300 V

## Material Specifications

**Conductor Material** Bare copper  
**Insulation Material** High density polyethylene (HDPE)  
**Jacket Material** PVC

## Environmental Specifications

**Operating Temperature** -20 °C to +60 °C (-4 °F to +140 °F)  
**Environmental Space** Non-plenum

## Packaging and Weights

**Cable weight** 229.177 kg/km | 154 lb/kft  
**Packaging Type** Reel

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

